



Outside Plant Fiber Optic Cable, HDPE, 12-fiber, Multimode, OM4, loose tube, gel-filled. Provides Rodent Resistance.

Product Classification

| | |
|------------------------------|------------------------------|
| Regional Availability | Australia/New Zealand EMEA |
| Portfolio | CommScope® |
| Product Type | Fiber OSP cable |
| Product Series | O-CA |

General Specifications

| | |
|-------------------------------------|--------------------------------------------------------------------------------------------------------------|
| Armor Type | Corrugated steel |
| Cable Type | Loose tube |
| Subunit Type | Gel-filled |
| Filler, quantity | 1 |
| Jacket Color | Black |
| Jacket Marking | Meters |
| Jacket Marking Method | Inkjet |
| Jacket Marking Text | COMMSCOPE GB SYSTEM F.O. CABLE X-599683-2 CSA GEL LOOSE TUBE 12x50/125 OM4 HDPE (Serial number) (metre mark) |
| Fibers per Subunit, quantity | 12 |
| Total Fiber Count | 12 |

Dimensions

| | |
|-----------------------------|----------------------|
| Cable Length | 2000 m 6,561.68 ft |
| Diameter Over Jacket | 10 mm 0.394 in |

Material Specifications

| | |
|------------------------|----------------------------------|
| Jacket Material | High density polyethylene (HDPE) |
|------------------------|----------------------------------|

Mechanical Specifications

| | |
|------------------------------------------|----------------------|
| Minimum Bend Radius, loaded | 200.7 mm 7.902 in |
| Minimum Bend Radius, unloaded | 160 mm 6.299 in |
| Tensile Load, long term, maximum | 625 N 140.506 lbf |
| Tensile Load, short term, maximum | 1200 N 269.771 lbf |
| Flex | 25 cycles |

Optical Specifications

| | |
|-------------------|-----------------|
| Fiber Type | OM4, LazrSPEED® |
|-------------------|-----------------|

Optical Specifications, Wavelength Specific

| | |
|-----------------------------|---------------------------------------------|
| Attenuation, maximum | 1.00 dB/km @ 1,300 nm 3.50 dB/km @ 850 nm |
| Standards Compliance | IEC 60794-1 TIA-492AAAD (OM4) |

Environmental Specifications

| | |
|---------------------------------|-------------------------------------|
| Installation temperature | -5 °C to +50 °C (+23 °F to +122 °F) |
| Operating Temperature | -20 °C to +70 °C (-4 °F to +158 °F) |
| Storage Temperature | -20 °C to +70 °C (-4 °F to +158 °F) |

Packaging and Weights

| | |
|---------------------|---------------------------|
| Cable weight | 104 kg/km 69.885 lb/kft |
|---------------------|---------------------------|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|---------------------------------------------------------------------------------------------------------------------------------|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |



Included Products

| | |
|----------|-------------------------------------------------------|
| CS-5K-LT | – LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber |
|----------|-------------------------------------------------------|

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber

LazrSPEED® 550

Product Classification

| | |
|---------------------|---------------|
| Portfolio | CommScope® |
| Product Type | Optical fiber |

General Specifications

| | |
|------------------------------------------------------|----------------------------------------|
| Cladding Diameter | 125 µm |
| Cladding Diameter Tolerance | ±0.8 µm |
| Cladding Non-Circularity, maximum | 1 % |
| Coating Diameter (Colored) | 254 µm |
| Coating Diameter (Uncolored) | 245 µm |
| Coating Diameter Tolerance (Colored) | ±7 µm |
| Coating Diameter Tolerance (Uncolored) | ±10 µm |
| Coating/Cladding Concentricity Error, maximum | 12 µm |
| Core Diameter | 50 µm |
| Core Diameter Tolerance | ±2.5 µm |
| Core/Clad Offset, maximum | 1.5 µm |
| Proof Test | 689.476 N/mm ² 100000 psi |

Mechanical Specifications

| | |
|-------------------------------------------------|---------------------------------------|
| Macrobending, 15 mm Ø mandrel, 2 turns | 0.20 dB @ 850 nm 0.50 dB @ 1,300 nm |
| Macrobending, 30 mm Ø mandrel, 2 turns | 0.10 dB @ 850 nm 0.30 dB @ 1,300 nm |
| Macrobending, 75 mm Ø mandrel, 100 turns | 0.50 dB @ 1,300 nm 0.50 dB @ 850 nm |
| Coating Strip Force, maximum | 8.9 N 2.001 lbf |
| Coating Strip Force, minimum | 1.3 N 0.292 lbf |
| Dynamic Fatigue Parameter, minimum | 18 |

CS-5K-LT

Optical Specifications

| | |
|--------------------------------------------|---------------------|
| Numerical Aperture | 0.2 |
| Numerical Aperture Tolerance | ±0.015 |
| Point Defects, maximum | 0.15 dB |
| Zero Dispersion Slope, maximum | 0.105 ps/[km-nm-nm] |
| Zero Dispersion Wavelength, maximum | 1316 nm |
| Zero Dispersion Wavelength, minimum | 1297 nm |

Optical Specifications, Wavelength Specific

| | |
|-------------------------------------|-------------------------------------------------------------------------------|
| 1 Gbps Ethernet Distance | 1,110 m @ 850 nm 600 m @ 1,300 nm |
| 10 Gbps Ethernet Distance | 550 m @ 850 nm |
| Attenuation, maximum | 1.00 dB/km @ 1,300 nm 3.00 dB/km @ 850 nm |
| Backscatter Coefficient | -68.0 dB @ 850 nm -75.7 dB @ 1,300 nm |
| Bandwidth, Laser, minimum | 4,700 MHz-km @ 850 nm 500 MHz-km @ 1,300 nm |
| Bandwidth, OFL, minimum | 3,500 MHz-km @ 850 nm 500 MHz-km @ 1,300 nm |
| Differential Mode Delay | 0.70 ps/m @ 850 nm 0.88 ps/m @ 1,300 nm |
| Differential Mode Delay Note | Superior to TIA-492AAAC and IEC 60793-2-10 at 850 nm |
| Index of Refraction | 1.479 @ 1,300 nm 1.483 @ 850 nm |
| Standards Compliance | IEC 60793-2-10, type A1a.3a IEC 60793-2-10, type A1a.3b TIA-492AAAD (OM4) |

Environmental Specifications

| | |
|----------------------------------------------|--------------------|
| Heat Aging, maximum | 0.20 dB/km @ 85 °C |
| Temperature Dependence, maximum | 0.1 dB/km |
| Temperature Humidity Cycling, maximum | 0.2 dB/km |
| Water Immersion, maximum | 0.20 dB/km @ 23 °C |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--------------------------------------------------------------------------------|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |



CS-5K-LT

* Footnotes

- Temperature Dependence, maximum** Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)
- Temperature Humidity Cycling, maximum** Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity