



Indoor/Outdoor Low Smoke Zero Halogen / 96F Microsheath Breakout Fiber Optic Cable - Black

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber indoor/outdoor cable
<b>Product Series</b>	C-LN


## General Specifications

<b>Cable Type</b>	Stranded microsheath tube
<b>Subunit Type</b>	Gel-free
<b>Jacket Color</b>	Black
<b>Jacket Marking</b>	Meters
<b>Jacket Marking Method</b>	Inkjet
<b>Jacket Marking Text</b>	0000M 8 x 12SM G.657.A1 SWE LSZH TDC -NET A/S - Lyslederkabel - GIV AGT - USYNLIGT LASERLYS COMMSCOPE UK [YYYY/WW] – [serial number]
<b>Subunit, quantity</b>	8
<b>Fibers per Subunit, quantity</b>	12
<b>Total Fiber Count</b>	96

## Dimensions

<b>Cable Length</b>	500 m   1,640.42 ft
<b>Buffer Tube/Subunit Diameter</b>	1.4 mm   0.055 in
<b>Diameter Over Jacket</b>	6.8 mm   0.268 in

## Representative Image



## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	100 mm   3.937 in
<b>Minimum Bend Radius, unloaded</b>	70 mm   2.756 in
<b>Tensile Load, long term, maximum</b>	200 N   44.962 lbf
<b>Tensile Load, short term, maximum</b>	900 N   202.328 lbf
<b>Cable Crush Resistance, maximum</b>	10 N/mm   57.101 lb/in
<b>Compression Test Method</b>	IEC 60794-1-21 E3
<b>Impact</b>	2 N-m   17.701 in lb
<b>Impact Test Method</b>	IEC 60794-1-21 E4
<b>Strain Test Method</b>	IEC 60794-1-21 E1
<b>Twist</b>	5 cycles
<b>Twist Test Method</b>	IEC 60794-1 E7

## Optical Specifications

<b>Fiber Type</b>	G.657.A1
-------------------	----------

## Optical Specifications, Wavelength Specific

<b>Attenuation, maximum</b>	0.25 dB/km @ 1,550 nm   0.27 dB/km @ 1,490 nm   0.27 dB/km @ 1,625 nm   0.36 dB/km @ 1,310 nm
<b>Standards Compliance</b>	TIA-492CAAB (OS2)

## Environmental Specifications

<b>Installation temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>EN50575 CPR Cable EuroClass Fire Performance</b>	Dca
<b>EN50575 CPR Cable EuroClass Smoke Rating</b>	s1a
<b>EN50575 CPR Cable EuroClass Droplets Rating</b>	d0
<b>EN50575 CPR Cable EuroClass Acidity Rating</b>	a1
<b>Environmental Space</b>	Universal Low Smoke Zero Halogen (ULSZH)
<b>Water Penetration</b>	336 h
<b>Water Penetration Test Method</b>	IEC 60794-1 F5

## Environmental Test Specifications

<b>Temperature Cycle</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Temperature Cycle Test Method</b>	IEC 60794-1-22 F1

## Packaging and Weights

<b>Cable weight</b>	47 kg/km   31.583 lb/kft
---------------------	--------------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## Included Products

CS-8F-LT	- Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber
----------	----------------------------------------------------------------------------

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable