# JF-CAPKIT



## 2.2-5 Female End Cap Assembly

### **Product Classification**

**Product Type** Surge arrestor accessory

Product Brand HELIAX®

General Specifications

**Interface** 2.2-5 Female


**Dimensions** 

**Length** 19 mm | 0.748 in

**Diameter** 18 mm | 0.709 in

## Outline Drawing

#### 2,2-5 FEMALE END CAP ASSEMBLY



**COMMSCOPE®** 

# JF-CAPKIT

Material Specifications

**Finish** Trimetal

Material Type Brass

Mechanical Specifications

**Coupling Nut Proof Torque** 4 N-m | 35.403 in lb

Interface Durability 50 cycles

Mechanical Shock Test Method IEC 60068-2-27

**Environmental Specifications** 

**Operating Temperature**  $-55 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-67 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$ 

Storage Temperature -65 °C to +125 °C (-85 °F to +257 °F)

**Attenuation, Ambient Temperature** 20 °C | 68 °F

**Average Power, Ambient Temperature** 40 °C | 104 °F

**Average Power, Inner Conductor Temperature** 100 W

Corrosion Test Method IEC 60068-2-11

Immersion Depth 1 m

Immersion Test Mating Mated

**Immersion Test Method** IEC 60529:2001, IP68

Moisture Resistance Test Method IEC 60068-2-3

Thermal Shock Test Method IEC 60068-2-14

Vibration Test Method IEC 60068-2-6

Packaging and Weights

Packaging quantity 1

**Weight, net** 24.24 g | 0.053 lb

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

Page 2 of 3



# JF-CAPKIT



\* Footnotes

**Immersion Depth** 

Immersion at specified depth for 24 hours

