



OCM8 Fiber Optic Splitter Module, Planar, 2x8 Splitter, singlemode, LC/APC, symmetrical split ratio, 2 m pigtailed

Product Classification

Regional Availability	Asia Australia/New Zealand China EMEA India Latin America North America
Product Type	Splitter module
Product Series	OCM8

General Specifications

Functionality	Splitting
Technology Type	Planar lightwave circuit (PLC)
Distribution Type	2 x 8 splitter
Interface, Input	LC
Interface, Output	LC
Interface Feature, Output	APC
Split Ratio	Symmetrical
Splitter, quantity	1

Dimensions

Height	5 mm 0.197 in
Depth	45 mm 1.772 in
Length	100 mm 3.937 in
Pigtail Length, Input	2 m 6.562 ft
Pigtail Length, Output	2 m 6.562 ft
Pigtail Diameter, Input	1.8 mm 0.071 in
Pigtail Diameter, Output	1.8 mm 0.071 in

Optical Specifications

Fiber Type	G.657.A1
Directivity, minimum	55 dB
Polarization Dependent Loss, maximum	0.3 dB
Uniformity, maximum	1.85 dB

760242984 | OCM8-SP128LLG-20DB

Wavelength Range	1260–1650 nm
Insertion Loss, Splitter, maximum	11.4 dB
Return Loss, Connector, minimum	55 dB

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
------------------------------	--------------------------------------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted

