


SP-16400NNNNXBBB | PLC 1X64 900UM NO CONN



Wideband PLC Splitter, singlemode, 1x64, symmetrical split ratio, 0.900 mm cable, no connectors

Product Classification

Regional Availability	Asia Australia/New Zealand China EMEA India Latin America North America
Product Type	Bare splitter

General Specifications

Device Type	Component, rectangular
Functionality	Splitting
Technology Type	Planar lightwave circuit (PLC)
Distribution Type	1 x 64 splitter
Interface, Input	Stub tail
Interface, Output	Stub tail
Split Ratio	Symmetrical
Splitter, quantity	1

Dimensions

Height	6 mm 0.236 in
Width	40 mm 1.575 in
Length	120 mm 4.724 in
Pigtail Length, Input	2.5 m 8.202 ft
Pigtail Length, Output	2.5 m 8.202 ft
Pigtail Diameter, Input	0.25 mm 0.01 in
Pigtail Diameter, Output	0.25 mm 0.01 in

Optical Specifications

Fiber Type	G.657.A2
Directivity, minimum	55 dB

SP-16400NNNNXBBB | PLC 1X64 900UM NO CONN

Polarization Dependent Loss, maximum	0.4 dB
Uniformity, maximum	2 dB
Wavelength Range	1260–1650 nm
Insertion Loss, Splitter, maximum	20.5 dB
Return Loss, Splitter, minimum	55 dB

Environmental Specifications

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	5%–95%, non-condensing

Packaging and Weights

Packaging quantity	1
---------------------------	---