SF-10207NNNNXBBB | FBT 1X2 93/07 900UM NO CONN



FBT Coupler, singlemode, 1x2 FBT, 93/07 split ratio, 0.900 mm cable, no connectors

Product Classification

Regional Availability

Asia | Australia/New Zealand | China | EMEA | India | Latin

America | North America

Product Type Bare splitter

General Specifications

Device Type Component, tubular

Functionality Splitting

Technology Type Fused biconic tapered

Distribution Type 1 x 2 splitter

Interface, Input Stub tail

Interface, Output Stub tail

Split Ratio 93/7

Splitter, quantity 1

Dimensions

Height 3.2 mm | 0.126 in

Length 55 mm | 2.165 in

Pigtail Length, Input 2.5 m | 8.202 ft

Pigtail Length, Output 2.5 m | 8.202 ft

Pigtail Diameter, Input 0.25 mm | 0.01 in

Pigtail Diameter, Output 0.25 mm | 0.01 in

Optical Specifications

Fiber TypeG.657.A1Directivity, minimum55 dB

Polarization Dependent Loss, maximum 0.2 dB



SF-10207NNNNXBBB | FBT 1X2 93/07 900UM NO CONN

Wavelength Range 1260–1360 nm | 1420–1625 nm

Insertion Loss, Primary Output, maximum0.6 dBInsertion Loss, Secondary Output, maximum13.5 dBReturn Loss, Splitter, minimum55 dB

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Relative Humidity 5%–95%, non-condensing

Packaging and Weights

Packaging quantity 1

