


# UQGRPSN7R

## Base Product



Ultra Low Loss (ULL) Singlemode G.657.A2 MPO16 (Non-Pinned) to SN, Fiber Array assembly, 16-Fiber, Plenum

## Product Classification

|                              |  |
|------------------------------|--|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   China   Europe   India   Latin America   Middle East/Africa   North America   |
| <b>Portfolio</b>             | CommScope®   |
| <b>Product Type</b>          | Fiber array cable assembly   |
| <b>Product Brand</b>         | Propel   SYSTIMAX ULL  |
| <b>Ordering Note</b>         | For additional jacket colors, please contact a CommScope Sales Representative   For lengths greater than 999 ft (304 m), orders must be in meters   Minimum length may vary based on cable configuration |

## General Specifications


|                                     |                         |
|-------------------------------------|-------------------------|
| <b>Connector A, quantity</b>        | 1                       |
| <b>Color, boot A</b>                | Black                   |
| <b>Color, connector A</b>           | Green                   |
| <b>Connector B, quantity</b>        | 8                       |
| <b>Color, boot B</b>                | Blue                    |
| <b>Color, connector B</b>           | Blue                    |
| <b>Construction Type</b>            | Stranded                |
| <b>Furcation Color</b>              | Yellow                  |
| <b>Interface, Connector A</b>       | MPO-16/APC Female       |
| <b>Interface, Connector B</b>       | SN/UPC                  |
| <b>Jacket Color</b>                 | Yellow                  |
| <b>Polarity</b>                     | Method B Enhanced (ULL) |
| <b>Fibers per Subunit, quantity</b> | 16                      |
| <b>Total Fibers, quantity</b>       | 16                      |

## Dimensions

# UQGRPSN7R

|   |   |
|---|---|
| <b>Breakout Length</b>                  | 12 in   24 in   36 in   48 in   60 in   72 in |
| <b>Cable Assembly Length Range (m)</b>  | 1 – 304                                       |
| <b>Cable Assembly Length Range (ft)</b> | 2 – 999                                       |

## Ordering Tree



## Mechanical Specifications

|  |                               |
|--|-------------------------------|
| <b>Cable Retention Strength, maximum</b> | 11.24 lb @ 0°   4.40 lb @ 90° |
|--|-------------------------------|

## Optical Specifications

|                   |                      |
|-------------------|----------------------|
| <b>Fiber Mode</b> | Singlemode           |
| <b>Fiber Type</b> | G.657.A2, TeraSPEED® |

## Environmental Specifications

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Operating Temperature</b> | -10 °C to +60 °C (+14 °F to +140 °F) |
| <b>Environmental Space</b>   | Indoor   Plenum                      |

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

## Included Products

|           |   |  |
|-----------|---|--|
| 460201084 | – | Fiber Optic Connector, SN/UPC for 1.6 mm cable |
|-----------|---|--|

# UQGRPSN7R

---

- 760249691  
P-016-MP-8G1-F30YL – Fiber indoor cable, Plenum MPO Light Duty for Patchcords, 16 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color
- 860661399 – Fiber Optic Connector Kit, singlemode, OS2, MPO-16/APC, ULL, unpinned, green, for 3 mm cable

# 460201084

---



Fiber Optic Connector, SN/UPC for 1.6 mm cable

## Product Classification

### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

### Portfolio

CommScope®

### Product Type

Fiber connector

## General Specifications

### Color, boot

Black

### Color, housing

Navy blue

### Interface

SN/UPC

## Dimensions

### Length

50.9 mm | 2.004 in

### Compatible Cable Diameter

1.5 mm | 0.059 in | 1.6 mm | 0.063 in

## Material Specifications

### Ferrule Material

Zirconia

## Mechanical Specifications

### Cable Retention Strength, maximum

11.24 lb @ 0 °

## Optical Specifications

### Fiber Mode

Singlemode

### Fiber Type

G.657.A2

### Optical Components Standard

ANSI/TIA-568. 3-D | IEC 61753-1


### Insertion Loss, maximum

0.25 dB

### Return Loss, minimum

50 dB

# 760249691 | P-016-MP-8G1-F30YL



Fiber indoor cable, Plenum MPO Light Duty for Patchcords, 16 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber indoor cable  |
| <b>Product Series</b>        | P-MP  |


## General Specifications

|                          |                 |
|--------------------------|-----------------|
| <b>Cable Type</b>        | MPO trunk cable |
| <b>Construction Type</b> | Non-armored     |
| <b>Subunit Type</b>      | Gel-free        |
| <b>Jacket Color</b>      | Yellow          |
| <b>Jacket Marking</b>    | Feet            |
| <b>Total Fiber Count</b> | 16              |

## Dimensions

|                             |                 |
|-----------------------------|-----------------|
| <b>Diameter Over Jacket</b> | 3 mm   0.118 in |
|-----------------------------|-----------------|

## Representative Image



## Mechanical Specifications

|  |                                       |
|--|---------------------------------------|
| <b>Minimum Bend Radius, loaded</b>       | 45 mm   1.772 in                      |
| <b>Minimum Bend Radius, unloaded</b>     | 24 mm   0.945 in                      |
| <b>Tensile Load, long term, maximum</b>  | 80 N   17.985 lbf                     |
| <b>Tensile Load, short term, maximum</b> | 267 N   60.024 lbf                    |
| <b>Compression</b>                       | 3.5 N/mm   19.986 lb/in               |
| <b>Compression Test Method</b>           | FOTP-41   IEC 60794-1 E3              |
| <b>Flex</b>                              | 300 cycles                            |
| <b>Flex Test Method</b>                  | FOTP-104   IEC 60794-1 E6             |
| <b>Impact</b>                            | 0.74 N-m   6.55 in lb                 |
| <b>Impact Test Method</b>                | FOTP-25   IEC 60794-1 E4              |
| <b>Strain</b>                            | See long and short term tensile loads |
| <b>Strain Test Method</b>                | FOTP-33   IEC 60794-1 E1              |
| <b>Twist</b>                             | 10 cycles                             |
| <b>Twist Test Method</b>                 | FOTP-85   IEC 60794-1 E7              |
| <b>Vertical Rise, maximum</b>            | 500 m   1,640.42 ft                   |

## Optical Specifications

|                   |                   |
|-------------------|-------------------|
| <b>Fiber Type</b> | G.657.A2/B2   OS2 |
|-------------------|-------------------|

## Environmental Specifications

|                                      |                                       |
|--------------------------------------|---------------------------------------|
| <b>Installation temperature</b>      | 0 °C to +70 °C (+32 °F to +158 °F)    |
| <b>Operating Temperature</b>         | 0 °C to +70 °C (+32 °F to +158 °F)    |
| <b>Storage Temperature</b>           | -40 °C to +70 °C (-40 °F to +158 °F)  |
| <b>Cable Qualification Standards</b> | ANSI/ICEA S-83-596   Telcordia GR-409 |
| <b>Environmental Space</b>           | Plenum                                |
| <b>Flame Test Listing</b>            | NEC OFNP (ETL) and c(ETL)             |
| <b>Flame Test Method</b>             | NFPA 130   NFPA 262                   |

## Environmental Test Specifications

|                             |                                    |
|-----------------------------|------------------------------------|
| <b>Heat Age</b>             | 0 °C to +85 °C (+32 °F to +185 °F) |
| <b>Heat Age Test Method</b> | IEC 60794-1 F9                     |
| <b>Low High Bend</b>        | 0 °C to +70 °C (+32 °F to +158 °F) |

# 760249691 | P-016-MP-8G1-F30YL

---

|                                      |                                    |
|--------------------------------------|------------------------------------|
| <b>Low High Bend Test Method</b>     | FOTP-37   IEC 60794-1 E11          |
| <b>Temperature Cycle</b>             | 0 °C to +70 °C (+32 °F to +158 °F) |
| <b>Temperature Cycle Test Method</b> | FOTP-3   IEC 60794-1 F1            |

## Packaging and Weights


|                     |                          |
|---------------------|--------------------------|
| <b>Cable weight</b> | 9.3 kg/km   6.249 lb/kft |
|---------------------|--------------------------|

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

# 860661399

---



Fiber Optic Connector Kit, singlemode, OS2, MPO-16/APC, ULL, unpinned, green, for 3 mm cable

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber connector   |

## General Specifications

|                          |                |
|--------------------------|----------------|
| <b>Color</b>             | Green          |
| <b>Color, boot</b>       | Black          |
| <b>Ferrule Geometry</b>  | Angled         |
| <b>Interface</b>         | MPO/APC Female |
| <b>Interface Feature</b> | Unpinned       |

## Dimensions

|                                  |                 |
|----------------------------------|-----------------|
| <b>Compatible Cable Diameter</b> | 3 mm   0.118 in |
|----------------------------------|-----------------|

## Optical Specifications

|                                |            |
|--------------------------------|------------|
| <b>Fiber Mode</b>              | Singlemode |
| <b>Fiber Type</b>              | OS2        |
| <b>Insertion Loss, maximum</b> | 0.3 dB     |

## Packaging and Weights

|                           |   |
|---------------------------|---|
| <b>Packaging quantity</b> | 1 |
|---------------------------|---|

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |



# 860661399

---

ROHS Compliant

UK-ROHS Compliant

