


# B-CN

---

Base Product



Fiber Optic Cable, Outdoor Micro Cable for Air-blown installation, Central Tube All-Dielectric


## Product Classification

|                              |                 |
|------------------------------|-----------------|
| <b>Regional Availability</b> | Europe          |
| <b>Portfolio</b>             | CommScope®      |
| <b>Product Type</b>          | Fiber OSP cable |
| <b>Product Series</b>        | B-CN            |

## General Specifications

|                          |             |
|--------------------------|-------------|
| <b>Cable Type</b>        | Microcable  |
| <b>Construction Type</b> | Non-armored |
| <b>Subunit Type</b>      | Gel-filled  |

## Representative Image



## Environmental Specifications

# B-CN

---

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| <b>Installation temperature</b>      | -10 °C to +60 °C (+14 °F to +140 °F) |
| <b>Operating Temperature</b>         | -20 °C to +60 °C (-4 °F to +140 °F)  |
| <b>Storage Temperature</b>           | -20 °C to +60 °C (-4 °F to +140 °F)  |
| <b>Cable Qualification Standards</b> | IEC 60794-1-2                        |
| <b>Environmental Space</b>           | Air-blown, microduct                 |
| <b>Jacket UV Resistance</b>          | UV stabilized                        |

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable