

FDT-CK348NXG1520-M



iFDT Indoor Fiber Distribution Terminal, 48-fiber, LC/UPC, soft-wall pigtails, mechanical splice trays, 152 m stub length

- Compact and secure family of enclosures by connecting fiber cables at MDUs
- Integrated splice trays offer flexible splice management for individual or mass splicing
- Dual-hinged design ensures separation of owner/client network segments
- Robust steel construction protects fibers against damage and ensures network reliability
- Slotted cable entrance ports allow for rapid cable installation and pass-through capability

Product Classification

Regional Availability	North America
Product Type	Fiber distribution terminal
Product Series	IFDT

General Specifications

Adapters, quantity	24
Cable Entry Location	Bottom right Top right
Cable Type	Pigtails - Stranded
Color	Putty white
Front Door Type	Double hinged
Growth Configuration	Fully loaded
Interface	LC/UPC
Lock Type	Padlock ready
Mounting	Wall
Port, quantity	48
Splice Tray Chip Type	Heat shrink
Splicing Capacity, maximum	48

Dimensions

Height	476.25 mm 18.75 in
Width	368.3 mm 14.5 in
Depth	127 mm 5 in

Ordering Tree

FDT-CK348NXG1520-M



Material Specifications

Finish	Powder coated
Material Type	Steel

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Environmental Space	Indoor
Qualification Standards	NEMA, Type 12 Telcordia GR-2898-CORE

Packaging and Weights

Packaging quantity	1
---------------------------	---

FDT-CK348NXG1520-M

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

