


UN874020304/10 | CS44PSD RED C6A 4/23 U /UTP RL 1KFT



CS44PSD ETL verified Category 6A U/UTP Cable, plenum, red jacket, 4 pair count, 1000 ft (305 m) length, reel

Product Classification

Regional Availability	North America
Portfolio	Uniprise®
Product Type	Twisted pair cable

General Specifications

Product Number	CS44PSD
ANSI/TIA Category	6A
Cable Component Type	Horizontal
Cable Type	U/UTP (unshielded)
Conductor Type, singles	Solid
Conductors, quantity	8
Jacket Color	Red
Note	Consult ANSI/TIA-568-C.2 Annex G for length de-rating guidance for cable installation in higher temperature environments
Pairs, quantity	4
Separator Type	Isolator
Transmission Standards	ANSI/TIA-568.2-D

Dimensions


Cable Length	304.8 m 1000 ft
Diameter Over Insulated Conductor	1.115 mm 0.044 in
Diameter Over Jacket, nominal	6.325 mm 0.249 in
Jacket Thickness	0.406 mm 0.016 in
Conductor Gauge, singles	23 AWG

Electrical Specifications

UN874020304/10 | CS44PSD RED C6A 4/23 U /UTP RL 1KFT

dc Resistance Unbalance, maximum	4 %
dc Resistance, maximum	8 ohms/100 m 2.438 ohms/100 ft
Dielectric Strength, minimum	1500 Vac 2500 Vdc
LP (Limited Power) Rating	0.7 A
Mutual Capacitance at Frequency	5.6 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	70 %
Operating Frequency, maximum	500 MHz
Operating Voltage, maximum	80 V
Remote Powering	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A

Representative Image



Electrical Cable Performance

CS	CommScope	NEXT	Near End Crosstalk (dB/100m)
STD	Refers to the standard value listed under Transmission Standards in the Electrical Specifications above	PSNEXT	Power Sum Near End Crosstalk (db/100m)
TYP	Typical Electrical Performance	ACRF	Attenuation to Crosstalk Ratio - Far End (dB/100m)
IL	Insertion Loss (dB/100m)	RL	Return Loss (dB)
ACR	Attenuation to Crosstalk Ratio (dB/100m)	ELTCTL	Equal Level Transverse Conversion Transfer Loss (dB/100m)
PSACR	Power Sum Attenuation to Crosstalk Ratio (dB/100m)		
PSACRF	Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)		
TCL	Transverse Conversion Loss (dB/100m)		

Freq. MHz	IL		NEXT		ACR		PSNEXT		PSACR		ACRF		PSACRF		RL	
	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP
1	2.1	1.9	74.3	88	72.2	86.1	72.3	86	70.2	84.1	67.8	89.1	64.8	86.9	20	32.6
4	3.8	3.5	65.3	77.8	61.5	74.3	63.3	75.8	59.5	72.4	55.8	77.9	52.8	76.1	23	33.6
8	5.3	4.8	60.8	73	55.4	68.2	58.8	71.1	53.4	66.3	49.7	72.2	46.7	70.3	24.5	34.1
10	5.9	5.4	59.3	71.7	53.4	66.3	57.3	69.4	51.4	64	47.8	70.3	44.8	68.3	25	34.6
16	7.5	7.1	56.2	68.2	48.8	61.2	54.2	66.3	46.8	59.2	43.7	66.1	40.7	64.1	25	37.5
20	8.4	7.9	54.8	66.5	46.4	58.5	52.8	64.4	44.4	56.5	41.8	64.3	38.8	62.3	25	36.3
25	9.4	8.9	53.3	65.3	44	56.4	51.3	63.3	42	54.4	39.8	62.4	36.8	60.5	24.3	34.4
31.25	10.5	10	51.9	63.2	41.4	53.2	49.9	61.4	39.4	51.4	37.9	60.3	34.9	58.5	23.6	34.1
62.5	15	14.2	47.4	58.8	32.4	44.6	45.4	56.8	30.4	42.6	31.9	54.3	28.9	52.1	21.5	32
100	19.1	18.1	44.3	55.7	25.2	37.6	42.3	53.7	23.2	35.6	27.8	50.5	24.8	48.2	20.1	28.3
155	24.1	22.6	41.4	52.7	17.4	30.1	39.4	50.8	15.4	28.2	24	46.9	21	44.8	18.8	25
200	27.6	25.8	39.8	50.3	12.2	24.5	37.8	48.4	10.2	22.6	21.8	44.6	18.8	42.3	18	22.9
250	31.1	29	38.3	49.1	7.3	20.1	36.3	47.1	5.3	18.1	19.8	42.6	16.8	40.4	17.3	21.2
300	34.3	31.9	37.1	47.8	2.9	16	35.1	45.9	0.9	14	18.3	40.2	15.3	38.1	16.8	19.9
350	37.2	34.8	36.1	46.3	-1.1	11.5	34.1	44.3	-3.1	9.5	16.9	39.4	13.9	37.3	16.3	18.8
400	40.1	37.4	35.3	45.4	-4.8	8	33.3	43.3	-6.8	5.9	15.8	37.1	12.8	34.8	15.9	17.9
450	42.7	39.6	34.5	44.2	-8.2	4.6	32.5	42	-10.2	2.5	14.7	36	11.7	33.8	15.5	17.2
500	45.3	41.8	33.8	42	-11.4	0.3	31.8	40	-13.4	-1.7	13.8	36.2	10.8	34.1	15.2	16.9
550		44.3		39.5		-4.9		37.8		-6.5		34.4		32.3		16.1
600		46.9		35.7		-11.2		34.6		-12.2		32.9		30.6		16
650		48.9		32		-16.9		31.4		-17.5		30.6		28.3		16

Material Specifications

Conductor Material	Bare copper
Insulation Material	FEP
Jacket Material	PVC
Separator Material	FEP
Tape Material	Poly/Aluminum/Poly

Mechanical Specifications

Pulling Tension, maximum 11.34 kg | 25 lb

Environmental Specifications

Installation temperature	0 °C to +60 °C (+32 °F to +140 °F)
Operating Temperature	-20 °C to +75 °C (-4 °F to +167 °F)
Environmental Space	Plenum
Temperature Rating, UL	105 °C 221 °F
Flame Test Method	CMP/FT6
Smoke Test Method	CMP/FT6

Packaging and Weights

Cable weight	58.038 kg/km 39 lb/kft
Packaging Type	Reel