

# CML-L30-63

---



Light Duty Chain Mount Kit, 14 in stand-off, 8 ft chain, includes pipe

**OBSOLETE**

## Product Classification

**Product Type** Chain mount kit

## General Specifications

**Chains, quantity** 2

**Pipe, quantity** 1

**Sectors, quantity** 1

## Dimensions

**Height** 152.4 mm | 6 in

**Width** 203.2 mm | 8 in

**Length** 1,600.2 mm | 63 in

**Chain Length** 2,400.3 mm | 94.5 in

**Pipe Length** 1,600.2 mm | 63 in

**Mounting Diameter, maximum** 762 mm | 30 in

**Mounting Diameter, minimum** 203.2 mm | 8 in

**Pipe Outer Diameter** 114.3 mm | 4.5 in

**Mounting Circumference, maximum** 2,392.68 mm | 94.2 in

**Mounting Circumference, minimum** 635 mm | 25 in

## Material Specifications

**Material Type** Hot dip galvanized steel

# CML-L30-63

---

## Mechanical Specifications

<b>Wind Rating</b>	120 mph (BWS) at 100 ft AGL
<b>Wind Rating Criteria</b>	One 96 in x 10 in panel antenna per sector
<b>Wind Rating Test Method</b>	TIA/EIA-222

## Packaging and Weights

<b>Included</b>	Brackets   Chains   Hardware   Pipe mount
<b>Packaging quantity</b>	1
<b>Weight, net</b>	59 kg   130.073 lb

## \* Footnotes

<b>Wind Rating</b>	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	--