

4

3


2

1

NOTES:

- 1.0 GENERAL
  - 1.1 ALL METRIC DIMENSIONS ARE IN BRACKETS
  - 1.2 FOR PATENTS, SEE WWW.CS-PAT.COM
- 2.0 DESIGN NOTES
- 3.0 MANUFACTURING/SPECIAL REQUIRMENTS
- 4.0 TEST
- 5.0 PACKAGING

REVISIONS				
REV.	ECN	DESCRIPTION	BY	DATE
A	8000030568	INITIAL RELEASE	RDLS	07/03/18
B	8000036044	ADDED XP-2035	ES	7/18/2019



PRODUCT	PLATE (QTY 1)	U-BOLT #1	QTY	U-BOLT #2	QTY
XP-2020	XPU01	GUB-4240	4	-	-
XP-2025	XPU01	GUB-4240	2	GUB-4352	2
XP-2030	XPU01	GUB-4240	2	GUB-4355	2
XP-2035	XPU02	GUB52440	2	GUB-53560	2
XP-2040	XPU02	GUB52440	2	GUB-5456	2
XP-2525	XPU01	GUB-4352	4	-	-
XP-2530	XPU01	GUB-4352	2	GUB-4355	2
XP-2540	XPU02	GUB-53045	2	GUB-5456	2
XP-3030	XPU01	GUB-4355	4	-	-
XP-3040	XPU02	GUB-53560	2	GUB-5456	2
XP-4040	XPU02	GUB-5456	4	-	-

B

<b>COMMSCOPE, INC. OF NORTH CAROLINA</b>										
TOLERANCES					SAP MATERIAL MASTER					
1 PLACE .X ± .25		3 PLACE .XXX ± 0.06			<b>SEE TABLE</b>					
2 PLACE .XX ± 0.12		ANGLES ± 2°								
FINISH GALV A123					MATERIAL A1011/A1018 GR 36					
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES INTERPRET PER ANSI Y 14.5M-1994	CE	ES	DATE	<b>XP SERIES</b>						
	RW	ES1081	07/18/2019							
	RV									
	AD	ES1081	07/18/2019							
	RE	ES1081	07/18/2019							
ECN 008000036044				SCALE	DOCUMENT NO.					
				<b>1:1</b>	<b>XP SERIES</b>					
SIZE		WORK AREA 24		MODEL			DRAWING			SHEET 1 OF 1
C			VERSION	STATUS	REVISION	VERSION	STATUS	REVISION		
			01	RE	B	01	RE	B		

DENSITY	0.28	lbs/in <sup>3</sup>
MASS	12.81	lbs
VOLUME	45.33	in <sup>3</sup>
SURFACE AREA		in <sup>2</sup>
HEIGHT		
LENGTH		
WIDTH		

4

3

2

1