

# MC-PK8-B

---

Low-Profile Co-location Platform Base Face Kit, 8 ft face, 15 in to 38 in OD, No Pipes or Support Rail



## Product Classification

**Product Type** Monopole platform kit

## General Specifications

**Mounting** Monopole, 381–965 mm (15–38 in) OD

**Pipe, quantity** 0

**Sectors, quantity** 3

## Dimensions

**Height** 254 mm | 10 in

**Face Width** 2.438 m | 8 ft

**Width** 2,438.4 mm | 96 in

**Length** 914.4 mm | 36 in

**Face Support Pipe Diameter** 88.9 mm | 3.5 in

**Mounting Diameter, maximum** 965.2 mm | 38 in

**Mounting Diameter, minimum** 304.8 mm | 12 in

**Pipe Outer Diameter** 0 mm | 0 in

**Stand-off Distance** 914.4 mm | 36 in

**Mounting Circumference, maximum** 962.66 mm | in

**Mounting Circumference, minimum** 378.46 mm | in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Mechanical Specifications

**Wind Rating** 120 mph (BWS) at 100 ft AGL | 140 mph (3-second gust) at 150 ft AGL using Exposure

# MC-PK8-B

---

D per FBC

**Wind Rating Criteria**

Four 72 in x 12 in panel antennas per sector

**Wind Rating Test Method**

TIA/EIA-222

## Environmental Specifications

**EPA with 1/2 in (12 mm) radial ice**

1.421 m<sup>2</sup> | 15.3 ft<sup>2</sup>

**EPA without ice**

1.533 m<sup>2</sup> | 16.5 ft<sup>2</sup>

## Packaging and Weights

**Included**

Platform | Ring mount

**Packaging quantity**

1

**Weight, net**

360.107 kg | 793.9 lb

## \* Footnotes

**Wind Rating**

BWS—Base Wind Speed; FBC—Florida Building Code

**EPA with 1/2 in (12 mm) radial ice**

EPA—Effective Projected Area

**EPA without ice**

EPA—Effective Projected Area