

# 760254919 | EPX-1U-PNL-OPEN

---



EPX 1U open sliding panel, accepts (3) LGX/PNL style splice cassettes, modules or panels, providing up to 36 duplex LC ports

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | Fiber patch panel   |
| <b>Product Series</b>        | EPX   |

## General Specifications

|  |  |
|--|--|
| <b>Application</b>                         | Accepts three LGX/1000 footprint panels/cassettes   Accepts three PNL-type adapter panels or ReadyPATCH® modules |
| <b>Color</b>                               | Black  |
| <b>Intelligence Type</b>                   | Not iPatch® ready  |
| <b>Interface, front</b>                    | Unloaded   |
| <b>Module/Adapter Pack Slots, quantity</b> | 3  |
| <b>Rack Type</b>                           | EIA 19 in  |
| <b>Rack Units</b>                          | 1  |
| <b>Shelf Movement</b>                      | Sliding  |
| <b>Total Fibers, quantity</b>              | 72   |
| <b>Total Ports, quantity</b>               | 0  |

## Dimensions

|               |                      |
|---------------|----------------------|
| <b>Height</b> | 44.45 mm   1.75 in   |
| <b>Width</b>  | 482.6 mm   19 in     |
| <b>Depth</b>  | 327.91 mm   12.91 in |

## Packaging and Weights

|                           |                   |
|---------------------------|-------------------|
| <b>Packaging quantity</b> | 1                 |
| <b>Weight, net</b>        | 1.179 kg   2.6 lb |

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

