



Fiber indoor/outdoor cable, LSZH Riser Distribution, 4 fiber single-unit, Singlemode G.652.D, Meters jacket marking, Black jacket color

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber indoor/outdoor cable
<b>Product Series</b>	C-DS

## General Specifications

<b>Cable Type</b>	Tight buffer
<b>Jacket Color</b>	Black
<b>Jacket Marking</b>	Meters
<b>Strength Members</b>	E-glass yarns
<b>Total Fiber Count</b>	4

## Dimensions

<b>Diameter Over Jacket</b>	4.8 mm   0.189 in
-----------------------------	-------------------

## Material Specifications

<b>Jacket Material</b>	Low Smoke Zero Halogen (LSZH)
<b>Inner Jacket Material</b>	Low Smoke Zero Halogen (LSZH)

## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	96 mm   3.78 in
<b>Minimum Bend Radius, unloaded</b>	48 mm   1.89 in
<b>Tensile Load, short term, maximum</b>	600 N   134.885 lbf
<b>Compression</b>	5 N/mm   28.551 lb/in
<b>Compression Test Method</b>	IEC 60794-1-21 E3
<b>Impact</b>	1 N-m   8.851 in lb
<b>Impact Test Method</b>	IEC 60794-1-21 E4
<b>Strain Test Method</b>	IEC 60794-1-21 E1

# 760255942 | C-004-DS-8M-MSUBK

---

<b>Twist</b>	10 cycles
<b>Twist Test Method</b>	IEC 60794-1-21 E7

## Optical Specifications

<b>Fiber Type</b>	G.652.D   OS2
-------------------	---------------

## Optical Specifications, Wavelength Specific

<b>Attenuation, maximum</b>	0.3 dB/km @ 1,550 nm   0.40 dB/km @ 1,310 nm
-----------------------------	--

## Environmental Specifications

<b>Installation temperature</b>	0 °C to +50 °C (+32 °F to +122 °F)
<b>Operating Temperature</b>	-10 °C to +70 °C (+14 °F to +158 °F)
<b>Storage Temperature</b>	-10 °C to +60 °C (+14 °F to +140 °F)
<b>Environmental Space</b>	Low Smoke Zero Halogen (LSZH)
<b>Flame Test Method</b>	IEC 60332-3-24
<b>Jacket UV Resistance</b>	UV stabilized
<b>Water Penetration</b>	24 h
<b>Water Penetration Test Method</b>	IEC 60794-1 F5C

## Environmental Test Specifications

<b>Temperature Cycle Test Method</b>	IEC 60794-1-22 F1
--------------------------------------	-------------------

## Packaging and Weights

<b>Cable weight</b>	20 kg/km   13.439 lb/kft
---------------------	--------------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



### \* Footnotes

# 760255942 | C-004-DS-8M-MSUBK

---

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable