

7844067-02 | WCS-2 DC



ERA® Wireless Communications Switch Subrack, 2 U -48Vdc, with integrated DCDC converter

This unit does not support CAT6A powered access points.

Product Classification

Product Type Subrack

Product Brand ERA®

General Specifications

Mounting Rack

Note Detailed Product Specifications are available. Please contact your local ANDREW representative.

Rack Type EIA 19 in

Slots Available, quantity 11

Dimensions

Height 88.5 mm | 3.484 in

Width 482 mm | 18.976 in

Depth 450 mm | 17.717 in

Packaging and Weights

Height, packed 540 mm | 21.26 in

Width, packed 600 mm | 23.622 in

Depth, packed 200 mm | 7.874 in

Included Fan filter | Fan tray

Weight, gross 10.6 kg | 23.369 lb

Weight, net 8.4 kg | 18.519 lb

Regulatory Compliance/Certifications

| Agency | Classification |
|------------|-----------------------------------|
| CHINA-ROHS | Above maximum concentration value |

7844067-02 | WCS-2 DC

ROHS Compliant/Exempted

UK-ROHS Compliant/Exempted

