


810010178/DB | L-024-LN-8F-M12YL/15D/B



Single Jacket All-Dielectric, Gel-Free, Indoor Stranded Microsheath Tube Cable

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America |
| Portfolio | CommScope® |
| Product Type | Fiber indoor cable |
| Product Series | L-LN |


General Specifications

| | |
|-------------------------------------|--|
| Cable Type | Stranded microsheat tube |
| Construction Type | Non-armored |
| Subunit Type | Gel-free |
| Filler, quantity | 3 |
| Jacket Color | Yellow |
| Jacket Marking | Custom printing |
| Jacket Marking Method | Inkjet |
| Jacket Marking Text | COMMSCOPE GB OPTICAL CABLE 810010178/DB 24 X G657A1 EN50575 CLASS C ULSZH [Serial number] [metre mark] |
| Subunit, quantity | 2 |
| Fibers per Subunit, quantity | 12 |
| Total Fiber Count | 24 |

Dimensions

| | |
|-------------------------------------|-------------------|
| Buffer Tube/Subunit Diameter | 1.5 mm 0.059 in |
| Diameter Over Jacket | 6.7 mm 0.264 in |

Representative Image



Material Specifications

Inner Jacket Material Low Smoke Zero Halogen (LSZH)

Mechanical Specifications

Minimum Bend Radius, unloaded 80 mm | 3.15 in
Tensile Load, long term, maximum 150 N | 33.721 lbf
Tensile Load, short term, maximum 480 N | 107.908 lbf
Compression 10 N/mm | 57.101 lb/in
Compression Test Method IEC 60794-1 E3
Impact 2 N-m | 17.701 in lb
Impact Test Method IEC 60794-1 E4
Strain See long and short term tensile loads
Strain Test Method IEC 60794-1 E1

Optical Specifications

Fiber Type G.657.A1, TeraSPEED®

Environmental Specifications

Installation temperature 0 °C to +50 °C (+32 °F to +122 °F)
Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

810010178/DB | L-024-LN-8F-M12YL/15D/B

| | |
|---|--------------------------------------|
| Storage Temperature | -40 °C to +70 °C (-40 °F to +158 °F) |
| Cable Qualification Standards | IEC 60794-1-2 |
| EN50575 CPR Cable EuroClass Fire Performance | B2ca |
| EN50575 CPR Cable EuroClass Smoke Rating | s1a |
| EN50575 CPR Cable EuroClass Droplets Rating | d0 |
| EN50575 CPR Cable EuroClass Acidity Rating | a1 |
| Environmental Space | Low Smoke Zero Halogen (LSZH) |

Environmental Test Specifications

| | |
|--------------------------------------|--------------------------------------|
| Temperature Cycle | -10 °C to +60 °C (+14 °F to +140 °F) |
| Temperature Cycle Test Method | IEC 60794-1 F1 |

Packaging and Weights

| | |
|---------------------|----------------------------|
| Cable weight | 48.8 kg/km 32.792 lb/kft |
|---------------------|----------------------------|

Included Products

| | | |
|----------|---|--|
| CS-8F-LT | - | Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber |
|----------|---|--|

* Footnotes

| | |
|------------------------------|---|
| Operating Temperature | Specification applicable to non-terminated bulk fiber cable |
|------------------------------|---|