

RRZZV6-65D-R10F



20-port sector antenna, 4x694-960 (R1 & R2), 4x1427-2690 (Y3 & Y5) and 12 x 1695-2690 MHz (Y1/Y2/Y4/Y6/Y7/Y8), 65° HPBW, 10xRET

- All Internal RET actuators are connected in "Cascaded SRET" configuration
- Supports re-configurable antenna sharing capability enabling control of the internal RET system using up to two separate RET compatible OEM radios
- Antenna shape optimized for wind load reduction

General Specifications

Antenna Type	Sector
Band	Multiband
Color	Light Gray (RAL 7035)
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radome Material	Fiberglass, UV resistant
Reflector Material	Aluminum
RF Connector Interface	4.3-10 Female
RF Connector Location	Bottom
RF Connector Quantity, mid band	16
RF Connector Quantity, low band	4
RF Connector Quantity, total	20

Remote Electrical Tilt (RET) Information


RET Hardware	CommRET v2
RET Interface	8-pin DIN Female 8-pin DIN Male
RET Interface, quantity	2 female 2 male
Input Voltage	10–30 Vdc
Internal RET	Low band (2) Mid band (8)
Power Consumption, active state, maximum	8 W
Power Consumption, idle state, maximum	1 W
Protocol	3GPP/AISG 2.0 (Single RET)

Dimensions

RRZZV6-65D-R10F

Width	498 mm 19.606 in
Depth	197 mm 7.756 in
Length	2688 mm 105.827 in
Net Weight, antenna only	46.1 kg 101.633 lb

Array Layout



Array ID	Frequency (MHz)	RF Connector	RET (SRET)	AISG No.	AISG RET UID
R1	694-960	1 - 2	1	AISG1	CPxxxxxxxxxxxxxxxxR1
R2	694-960	3 - 4	2	AISG1	CPxxxxxxxxxxxxxxxxR2
Y3	1427-2690	5 - 6	3	AISG1	CPxxxxxxxxxxxxxxxxY3
Y5	1427-2690	7 - 8	4	AISG1	CPxxxxxxxxxxxxxxxxY5
Y1	1695-2690	9 - 10	5	AISG1	CPxxxxxxxxxxxxxxxxY1
Y2	1695-2690	11 - 12	6	AISG1	CPxxxxxxxxxxxxxxxxY2
Y4	1695-2690	13 - 14	7	AISG1	CPxxxxxxxxxxxxxxxxY4
Y6	1695-2690	15 - 16	8	AISG1	CPxxxxxxxxxxxxxxxxY6
Y7	1695-2690	17 - 18	9	AISG1	CPxxxxxxxxxxxxxxxxY7
Y8	1695-2690	19 - 20	10	AISG1	CPxxxxxxxxxxxxxxxxY8

(Sizes of colored boxes are not true depictions of array sizes)

Port Configuration



Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	1427 – 2690 MHz 1695 – 2690 MHz 694 – 960 MHz
Polarization	±45°
Total Input Power, maximum	900 W @ 50 °C

RRZZV6-65D-R10F

Electrical Specifications

	R1,R2	R1,R2	R1,R2	Y1,Y2,Y4,Y6,Y7,Y8
Frequency Band, MHz	698–806	790–896	890–960	1695–1990
RF Port	1,2,3,4	1,2,3,4	1,2,3,4	9 to 20
Gain at Mid Tilt, dBi	16.2	16.3	16.3	16.4
Beamwidth, Horizontal, degrees	67	62	63	70
Beamwidth, Vertical, degrees	8.5	7.6	7	7.3
Beam Tilt, degrees	2–13	2–13	2–13	2–12
USLS (First Lobe), dB	19	20	24	16
Front-to-Back Ratio at 180°, dB	35	31	31	34
Front-to-Back Total Power at 180° ± 30°, dB	23	22	22	29
CPR at Boresight, dB	31	24	24	23
CPR at Sector, dB	10	7	8	8
Isolation, Cross Polarization, dB	28	28	28	25
Isolation, Inter-band, dB	28	28	28	25
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153	-153
Input Power per Port at 50°C, maximum, watts	250	250	250	200

Electrical Specifications, BASTA

	698–806	790–896	890–960	1695–1990
Frequency Band, MHz	698–806	790–896	890–960	1695–1990
Gain by all Beam Tilts, average, dBi	16	16.1	16.1	16.2
Gain by all Beam Tilts Tolerance, dB	±0.4	±0.4	±0.4	±0.8
Beamwidth, Horizontal Tolerance, degrees	±4	±3	±4	±6
Beamwidth, Vertical Tolerance, degrees	±0.6	±0.5	±0.5	±0.7
USLS, beampeak to 20° above beampeak, dB	17	16	18	16

Electrical Specifications

	Y1,Y2,Y4,Y6,Y7,Y8	Y1,Y2,Y4,Y6,Y7,Y8	Y1,Y2,Y4,Y6,Y7,Y8	Y3,Y5
Frequency Band, MHz	1920–2300	2300–2500	2490–2690	1427–1518
RF Port	9 to 20	9 to 20	9 to 20	5,6,7,8

RRZZV6-65D-R10F

Gain at Mid Tilt, dBi	17.3	17.9	18.1	15.3
Beamwidth, Horizontal, degrees	62	56	56	66
Beamwidth, Vertical, degrees	6.5	5.7	5.3	9.2
Beam Tilt, degrees	2–12	2–12	2–12	2–12
USLS (First Lobe), dB	17	20	21	17
Front-to-Back Ratio at 180°, dB	33	31	31	34
Front-to-Back Total Power at 180° ± 30°, dB	28	27	27	28
CPR at Boresight, dB	22	20	20	22
CPR at Sector, dB	6	6	4	9
Isolation, Cross Polarization, dB	25	25	25	25
Isolation, Inter-band, dB	25	25	25	25
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153	-153
Input Power per Port at 50°C, maximum, watts	200	200	200	200

Electrical Specifications, BASTA

Frequency Band, MHz	1920–2300	2300–2500	2490–2690	1427–1518
Gain by all Beam Tilts, average, dBi	17.1	17.7	17.8	15.2
Gain by all Beam Tilts Tolerance, dB	±0.7	±0.5	±0.5	±0.4
Beamwidth, Horizontal Tolerance, degrees	±7	±3	±5	±9
Beamwidth, Vertical Tolerance, degrees	±0.6	±0.3	±0.2	±0.6
USLS, beampeak to 20° above beampeak, dB	17	17	17	15

Electrical Specifications

	Y3,Y5	Y3,Y5	Y3,Y5	Y3,Y5
Frequency Band, MHz	1695–1990	1920–2300	2300–2500	2490–2690
RF Port	5,6,7,8	5,6,7,8	5,6,7,8	5,6,7,8
Gain at Mid Tilt, dBi	16.7	17.4	18	17.9
Beamwidth, Horizontal, degrees	62	55	52	53
Beamwidth, Vertical, degrees	7.5	6.8	6	5.5
Beam Tilt, degrees	2–12	2–12	2–12	2–12
USLS (First Lobe), dB	16	16	16	17
Front-to-Back Ratio at 180°, dB	38	37	34	34

RRZZV6-65D-R10F

Front-to-Back Total Power at 180° ± 30°, dB	32	31	29	28
CPR at Boresight, dB	21	21	25	22
CPR at Sector, dB	8	5	6	2
Isolation, Cross Polarization, dB	25	25	25	25
Isolation, Inter-band, dB	25	25	25	25
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153	-153
Input Power per Port at 50°C, maximum, watts	200	200	200	200

Electrical Specifications, BASTA

Frequency Band, MHz	1695–1990	1920–2300	2300–2500	2490–2690
Gain by all Beam Tilts, average, dBi	16.6	17.3	17.8	17.5
Gain by all Beam Tilts Tolerance, dB	±0.7	±0.5	±0.6	±0.8
Beamwidth, Horizontal Tolerance, degrees	±7	±7	±5	±9
Beamwidth, Vertical Tolerance, degrees	±0.6	±0.7	±0.5	±0.3
USLS, beampeak to 20° above beampeak, dB	15	15	15	15

Mechanical Specifications

Wind Loading @ Velocity, frontal	914.0 N @ 150 km/h (205.5 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	239.0 N @ 150 km/h (53.7 lbf @ 150 km/h)
Wind Loading @ Velocity, maximum	1,215.0 N @ 150 km/h (273.1 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	629.0 N @ 150 km/h (141.4 lbf @ 150 km/h)
Wind Speed, maximum	241 km/h (150 mph)

Packaging and Weights

Width, packed	565 mm 22.244 in
Depth, packed	318 mm 12.52 in
Length, packed	2809 mm 110.591 in

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

RRZZV6-65D-R10F

ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

- BSAMNT-2F – Mounting bracket for cylindrical pipe installations (60-115mm pipe diameter) for fix mechanical tilt applications.

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance