

# SRC9-U5A1F1CN000



NOVUX™ Specialty Range Closure 10, splice only, no adapters, no splitters, 4 splices, ANT splice protectors, black, 2x CR cable retention clip (Round cable : Range 4 to 6.2 mm & Flat cable : Range 3 x 5 to 4 x 8 mm)

- Modern drop solution offering providers the agility and flexibility to use it in last-mile fiber network applications, both above and below ground
- Protected from harsh conditions by CommScope's Octopus gel sealing technology
- Agnostic to connectivity technologies: splice, connector, field-installable connector for agility and flexibility
- Identification plate for either QR code or customer logo
- QR code and CommScope cTrak® app for one-click access to all product information

## Product Classification

<b>Regional Availability</b>	Asia   EMEA   Latin America   North America
<b>Regional Availability Note</b>	Contact your local CommScope representative for specific availability
<b>Product Type</b>	Single-ended, rectangular fiber closure
<b>Product Brand</b>	NOVUX™
<b>Product Series</b>	SRC10

## General Specifications

<b>Cable Capacity, Drop</b>	2 Flat 8.0 x 4.5 mm (0.30 x 0.17 in)   2 Round 2–6.2 mm (0.08–0.24 in)
<b>Cable Ports Quantity, total</b>	2 round ports
<b>Cable Sealing Type</b>	Compressed gel
<b>Cable Termination Attachments, quantity</b>	2
<b>Closure Sealing Type</b>	Hinged with latch
<b>Closure Style</b>	In-line
<b>Color</b>	Black
<b>Mounting</b>	Handhole   Partially buried   Pedestal   Wall/Pole Mount, mounting kit included
<b>Network Area Type</b>	Drop
<b>Port, quantity</b>	2
<b>Splice Tray Included, quantity</b>	1
<b>Splicing Capacity, Mass Fusion, maximum</b>	12
<b>Splicing Capacity, maximum</b>	4

# SRC9-U5A1F1CN000

---

<b>Splicing Capacity, Single Fusion, maximum</b>	4
<b>Splicing Type, Supported</b>	Single fusion
<b>Splitter Type</b>	No splitter

## Dimensions

<b>Width</b>	76 mm   2.992 in
<b>Depth</b>	26 mm   1.024 in
<b>Length</b>	210 mm   8.268 in
<b>Cable Entry Drop Port Diameter</b>	6 mm (0.24 in) mm

## Material Specifications

<b>Material Type</b>	Impact-resistant polymer
----------------------	--------------------------

## Optical Specifications

<b>Fiber Type</b>	G.657.A1   G.657.A2   G.657.B3
-------------------	--------------------------------

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Environmental Space</b>	Above ground   Below ground   Direct burial
<b>Qualification Standards</b>	IEC 60529, IP68 + 1 m waterhead   IEC 61753-1, category G
<b>UV Resistance</b>	UV stabilized

## Packaging and Weights

<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Box   Carton
<b>Weight, net</b>	0.157 kg   0.346 lb