

MTC38523L



Field Adjustable Monopole Load Distribution Reinforcement Kit, 3 Sector, 30" to 60" OD, 10' Adjustable Kicker

Product Classification

Product Type Reinforcement kit

General Specifications

Mounting Monopole, 762–1524 mm (30–60 in) OD

Sectors, quantity 3

Dimensions

Height 254 mm | 10 in

Length 3048 mm | 120 in

Mounting Diameter, maximum 1524 mm | 60 in

Mounting Diameter, minimum 762 mm | 30 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative

Packaging and Weights

Included Attachment hardware | Ring mount

Packaging quantity 1

Weight, net 246.754 kg | 544 lb

* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code