



- 1.0 GENERAL NOTES
 1.1 ALL IMPERIAL DIMENSIONS ARE IN BRACKETS [X.XX]
 1.2 MARK PART WITH IDENTIFICATION NUMBER
- 2.0 DESIGN NOTES
 2.1 DESIGNED PER CUSTOMER REQUIREMENTS
- 3.0 MANUFACTURING/SPECIAL REQUIREMENTS
 3.1 TIGHTEN ALL BOLTS SECURING FLAT PLATES BY THE TURN-OF-NUT METHOD. TIGHTEN ALL U-BOLTS USING TURN-OF-NUT METHOD WITH ATTENTION TO LEAVE EQUAL DISTANCE AND EQUAL FORCE ON EACH LEG OF THE U-BOLT.
- 4.0 TEST
- 5.0 PACKAGING
 5.1 PACKAGING SHALL MEET COMMScope REQUIREMENTS PER DOCUMENT IS-PL-3005
 5.2 PRINTED DOCUMENT TO BE PLACED INSIDE POLYBAG AND THEN IN SHIPPING CONTAINER
 5.3 EXTRA HARDWARE MAYBE SUPPLIED, BAGGED AND SHIPPED

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	JL1183 01SEP22	VICENTE 40155958CMO



COMPONENT PART NUMBERS PROVIDED FOR ASSEMBLY PURPOSES;
 INDIVIDUAL COMPONENTS MAY BE SHIPPED AS PARTS WITHIN AN INCLUDED KIT.

ITEM NO.	PART NO.	DESCRIPTION	QTY.	NOTE NO.
1	CM-1460	WELDMENT, COLLAR MOUNT	4	
2	MT38248	5/8" X 48" GALV THREADED ROD	8	
3	GWF-05	5/8" GALV FLAT WASHER, 1.7OD	16	
4	GWL-05	5/8" GALV LOCK WASHER	16	
5	GN-05	5/8" GALV HEX NUT	16	

DENSITY	0.07	lbs/in ³
MASS	164.58	lbs
VOLUME	2108.85	in ³
SURFACE AREA	11163.3	in ²
DENSITY	0.0022	g/mm ³
MASS	74811.0097	grams
VOLUME	34559950.0091	mm ³
SURFACE AREA	7202109.2737	mm ²
HEIGHT	1737[68.4]	
LENGTH	1737[68.4]	
WIDTH	302[11.8]	

COMMScope, INC. OF NORTH CAROLINA

TOLERANCES		SAP MATERIAL MASTER	
0 PLACE	X[.X] ± 6[0.25]	2 PLACE	.XX[.XXX] ± 1.50[0.06]
1 PLACE	.X[.XX] ± 3.0[0.12]	ANGLES	± 2°

FINISH: GALV A123 MATERIAL: _____

REV.	NAME	DATE	TITLE
CE	JL1183	01SEP22	4-SIDED COLLAR MOUNT ASSEMBLY
RW	JL1183	09/08/2022	
AD	VCORTEZ1	09/14/2022	
RE	JL1183	09/15/2022	

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN MILLIMETERS
INTERPRET PER ANSI Y 14.5M-1994

SCALE: 1:10 DOCUMENT NO: **VZWSMART-PLK7Q**

SIZE	Auth Group	INSL	MODEL	DRAWING		SHEET
A2			VERSION	STATUS	REVISION	1 OF 1
			00	RE	A	