

NOVUX<sup>™</sup> Prodigy<sup>™</sup> Hardened Indexing Terminal, Prodigy Adapter ports, 12F, 1:8 Splitter, 1 Forward port, Dielectric flat loose tube, 250 ft/76 m HMFOC Plug (female/no pin) tail

- NOVUX™ Hardened Multi-fiber Terminals incorporate hardened connector technology that is designed to withstand the rugged outside plant environment
- Hardened connectors are factory-integrated and environmentally sealed for use in optical drop cable deployments
- Plug-and-play adapter ports ensure rapid cable installment in the outside plant access section of the network
- NOVUX™ Prodigy™ HXT fiber indexing terminals are available with 1:4 or 1:8 splitter and optional multi-use ports, Index Only and Index Branching 2 to 6 fiber solutions
- Available stubless or with flat dielectric and flat toneable/locatable dielectric cable with HMFOC Plug (female/no pin)
- NOVUX™ Prodigy™ smaller terminal size for aesthetics and allowing installation in constrained spaces
- NOVUX™ Prodigy™ terminals are available in Black (RAL# 9005) or Gray (RAL# 7035)
- CommScope Product ID plate with QR code link to product documents and C-Track

#### **Product Classification**

Regional Availability

Asia | EMEA | Latin America | North America

Product Type Access terminal, with splitter/tap

Product Brand NOVUX™

Product Series HXT

Minimum Order Quantity 1

### General Specifications

Cable Type Dielectric - Flat - Loose Tube

Cable, quantity

**Distribution Type** 1 x 8 splitter

**Drop Port Type**Hardened Prodigy SC/APC

Drop Port, quantity 6

Enclosure Color Black (RAL 9005)

Forward Port Type Hardened multi-fiber (HMFOC) jack, male/pinned

Forward Port, quantity

Mounting Handhole | Pedestal | Pole | Strand

**COMMSCOPE®** 

Port Type Hardened Prodigy SC/APC

Port, quantity

Splitter, quantity

Stub Type Hardened multi-fiber (HMFOC) plug, female/no pin

9

1

**Dimensions** 

 Height
 80 mm | 3.14 in


 Width
 128 mm | 5.03 in


 Length
 207 mm | 8.14 in

Cable Length, stub 250 ft (76 m)

**Cable Outer Diameter** 4.3 x 8.0 mm (0.17 x 0.31 in) in

### Dimension Drawing






Port Configuration

**COMMSCOPE®** 

NOVUXHT	TECHNOLOGIES AVAILABLE	SMALL	MEDIUM	LARGE
HXT Series	Fiber indexing	12 fiber index only, 1f	12 fiber 1:4	12 fiber 1:8
		12 fiber index only, 2f	12f multi-use 2f + 1:4	12 fiber multi-use, 3f +1:4
		12 fiber index only, 3f	24f multi-use 2f	12 fiber multi-use, 4f +1:4
		12 fiber index only, 4f	24f multi-use 3f	12 fiber multi-use, 2f +1:8
		12 fiber multi-use, 2f	24f multi-use 4f	
		12 fiber branching, 2 to 6f per port		

#### Ordering Tree



### Material Specifications

Enclosure Material Type Hardened plastic

**Optical Specifications** 

**Fiber Type** G.657.A1/A2

**Operating Wavelength Range** 1260 – 1635 nm

**Attenuation Single Ports, maximum** 10.8 dB

Attenuation Cable Coefficient, maximum 0.30 dB/km @ 1550 nm | 0.40 dB/km @ 1310 nm

Attenuation Terminal Connectors, maximum 0.4 dB
Insertion Loss, Splitter, maximum 10.4 dB

Page 3 of 4



Insertion Loss, Stub Connector, maximum0.65 dBReturn Loss, Connector, maximum65 dBReturn Loss, Single Ports, minimum55 dB

### **Environmental Specifications**

Operating Temperature  $-40 \,^{\circ}\text{C}$  to  $+65 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+149 \,^{\circ}\text{F}$ )

**Relative Humidity** 5%–100%, condensing

Environmental Space Above ground | Below ground

Qualification Standards IEC 60529, IP68 + 2 m waterhead | IEC 61753-1, category G

**UV Resistance** UV stabilized

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Coiled

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



