

MTC3792U



Full Grating Monopole Co-location Platform Kit with Gates and Top Rail Kit, 10 in to 30 in OD, 12 ft 6 in face, includes twelve 2-3/8in OD x 96 in pipes

Product Classification

Product Type Co-location platform

General Specifications

Mounting Monopole, 254–762 mm (10–30 in) OD

Pipe, quantity 12

Sectors, quantity 3

Dimensions

Height 2,438.4 mm | 96 in

Face Width 3.81 m | 12.5 ft

Width 3810 mm | 150 in

Pipe Length 2,438.4 mm | 96 in

Mounting Diameter, maximum 762 mm | 30 in

Mounting Diameter, minimum 254 mm | 10 in

Pipe Outer Diameter 60.96 mm | 2.4 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact steelproducts@commscope.com or call 800-255-1479

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

MTC3792U

Included	Grating Plain end pipes (12) Platform Rail Ring mount
Packaging quantity	1
Weight, net	1,024.166 kg 2,257.9 lb

* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	--