

# FOSC-650

## Base Product



## FOSC650 Fiber Optic Splice Closures

- Single-ended base with four-latches dome design and reliable cable attachment system
- There are 3 cable segments: 2 for use with the small gel seal blocks/entrance ports and 1 for use with the large gel seal blocks/entrance ports
- Fully removable base for easy cable access during installation and provisioning
- Superior gel sealing technology incorporated in interchangeable and fully wrap around gel segments
- Compatible with a wide range of fiber cable sizes and types

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Product Type</b>	Single-ended, square fiber closure
<b>Product Brand</b>	FOSC®

## General Specifications


<b>Cable Entry Drop Port Style</b>	Gel block
<b>Cable Entry Main Port Style</b>	Gel block
<b>Cable Ports Quantity, total</b>	3 multi-out ports (12 cables)
<b>Cable Sealing Type</b>	Compressed gel
<b>Closure Sealing Type</b>	Over-centered latches with rubber gasket
<b>Closure Style</b>	Single-ended
<b>Color</b>	Black
<b>Mounting</b>	Pole   Strand   Wall
<b>Network Area Type</b>	Feeder   Trunk
<b>Splicing Type, Supported</b>	Mass fusion   Single fusion

## Dimensions

<b>Height</b>	345.44 mm   13.6 in
<b>Width</b>	345.44 mm   13.6 in
<b>Length</b>	900.43 mm   35.45 in
<b>Length, with trigger</b>	1,050.29 mm   41.35 in
<b>Main Cable Diameter, maximum</b>	40.64 mm   1.6 in


# FOSC-650




## Dimension Drawing



## Port Configuration

# FOSC-650



Gel Seals	Upper -Small Ports-		Lower -Large Ports-	
	# Ports	Cable Outside Diameter Min. - Max.	# Ports	Cable Outside Diameter Min. - Max.
Small 3-way 	2	8 - 20 mm 0.32 - 0.79 inch	1	25 - 35 mm 1.0 - 1.38 inches
Small 4-way 	2	8 - 22 mm 0.32 - 0.87 inch	2	10 - 28 mm 0.39 - 1.1 inches
Large 4-way 	2	18 - 25 mm 0.7 - 1.0 inch	2	25 - 40 mm 1.0 - 1.6 inches

## Material Specifications

**Material Type** Rugged polymer

## Environmental Specifications

**Environmental Space** Below ground | Buried

**Qualification Standards** IEC 60529, IP68 + 5 m waterhead

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Box | Carton

## Regulatory Compliance/Certifications

# FOSC-650

---

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system