

# FD-PANELS

## Base Product



### FD Fiber patch panel

- Provide ultra-high density patching to achieve maximum density of 160 LC fiber connections in 2RU
- FD fiber panels are offered in singlemode and multimode configurations

FD patch panels interface with QSFP ports to easily break them out in LC connections. The MPO and LC ports are both front facing for easy mapping and patching.

FD Patch panels are offered in 1RU and 2RU versions with method A and method B polarity configurations.

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber patch panel
Product Series	FD

## General Specifications

Color	Black
Interface, front	LC/UPC   MPO
Patch Cord Routing	Left sided   Right sided
Rack Type	EIA 19 in
Shelf Movement	Fixed

## Optical Specifications

Fiber Mode	Multimode   Singlemode
------------	------------------------

## Environmental Specifications

Safety Standard	UL 60950
-----------------	----------

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

# FD-PANELS

---

ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

