

# L7-CLAMP-3B

---



KwikClamp™ Hanger for 1-5/8 in coaxial cable, triple stack; includes hardware

## Product Classification

|                      |  |
|----------------------|--|
| <b>Product Type</b>  | Hanger kit   |
| <b>Product Brand</b> | KwikClamp™   |
| <b>Ordering Note</b> | CommScope® standard product in Europe, the Middle East, and Africa |

## General Specifications

|                          |   |
|--------------------------|---|
| <b>Cables per Hanger</b> | 1   |
| <b>Color</b>             | Black                                     |
| <b>Hanger Type</b>       | KwikClamp™ hanger                         |
| <b>Mounting</b>          | 3–25 mm flat plate   Round Member 8-25 mm |

## Dimensions

|                                     |                    |
|-------------------------------------|--------------------|
| <b>Maximum Stack Height</b>         | 3                  |
| <b>Height</b>                       | 282 mm   11.102 in |
| <b>Width</b>                        | 69 mm   2.717 in   |
| <b>Length</b>                       | 44 mm   1.732 in   |
| <b>Compatible Diameter, maximum</b> | 50.8 mm   2 in     |
| <b>Compatible Diameter, minimum</b> | 49 mm   1.929 in   |
| <b>Nominal Size</b>                 | 1-5/8 in           |
| <b>Hanger Spacing, maximum</b>      | 1.83 m   6.004 ft  |

## Electrical Specifications

|                                    |        |
|------------------------------------|--------|
| <b>Return Loss Effect, maximum</b> | 0.1 dB |
| <b>DTF Effect, maximum</b>         | 0.1 dB |

# L7-CLAMP-3B

---

## Material Specifications

**Material Type** Engineered plastic | Stainless steel

## Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

## Environmental Specifications

**Operating Temperature** -40 °C to +70 °C (-40 °F to +158 °F)

**Corrosion Resistance, minimum with no degradation** ≥500 hours in salt spray chamber

**Environmental Strength Capability** Five times cable weight

**UV Resistance, minimum with no degradation** ≥100 hours exposure in accelerated UV life chamber

## Packaging and Weights

**Height, packed** 15.5 cm | 6.102 in

**Width, packed** 30.5 cm | 12.008 in

**Length, packed** 35.5 cm | 13.976 in

**Included** Hardware

**Packaging quantity** 9

**Weight, gross** 3.66 kg | 8.069 lb

## Regulatory Compliance/Certifications

| Agency     | Classification   |
|------------|--|
| CHINA-ROHS | Below maximum concentration value  |
| REACH-SVHC | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS       | Compliant  |
| UK-ROHS    | Compliant  |



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power