	4	3	
D	 1.0 GENERAL NOTES 1.1 ALL METRIC DIMENSIONS ARE IN BRACKETS [X. X] 1.2 FOR PATENT INFO: https://www.cs-pat.com 2.0 DESIGN NOTES 3.0 MANUFACTURING/SPECIAL REQUIREMENTS 3.1 BUS BAR SHOWN IN VARIOUS MOUNTING CONFIGURATIONS 3.2 TIGHTEN ALL BOLTS SNUG TIGHT, DEFINED AS THE CONDITION OB ASSEMBLER USING AN ORDINARY SPUD WRENCH TO BRING THE C 4.0 TEST 5.0 PACKAGING 5.1 PACKAGING SHALL MEET COMMSCOPE REQUIREMENTS PER DOCU 5.2 PRINTED DOCUMENT TO BE PLACED INSIDE POLYBAG AND THEN IN 5.3 EXTRA HARDWARE MAY BE SUPPLIED, BAGGED AND SHIPPED 	JMENT IS-PL-3005	
		(8	
С		7	DOODOOOOOOOOOOOOOOOOOOOOOOOOOOOOOOOOOO
В	INSULATED SHELTER METHOD		3


COMPONENT PART NUMBERS PROVIDED FOR ASSEMBLY PURPOSES; INDIVIDUAL COMPONENTS MAY BE SHIPPED AS PARTS WITHIN AN INCLUDED KIT.

	ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	WEIGHT	NOTE NO.
А	1	GB0210G-00	GROUND BUS BAR, 2"X10", GALV	1	1.12 LBS	
	2	45840G-1	HANGER CLAMP	2	0.38 LBS	
	3	MT520	INSULATOR W/ 3/8" INSERT	2	0.21 LBS	
	4	SB0305	3/8" X 5/8" SS BOLT	4	0.04 LBS	
	5	SWL-03	3/8" SS LOCK WASHER	4	0.01 LBS	
	6	MT500GDP	STANDOFF BRACKET	2	0.33 LBS	
	7	DPA141ZP	6.5 X 25mm DRIVE PIN ANCHOR	4	0.02 LBS	
	8	GB0316-4	SQUARE HEAD SET SCREW, 3/8-16X1-3/4	2	0.07 LBS	


C 2023 CommScope, Inc. Confidential


3

			•				
REVISIONS							
REV.		DESCRIPTION		DATE	APPROVED		
А		INITIAL RELEASE		LL1090 30OCT23	AG1119 40182025CMO		



2





D

С

В